



1/4 turn nozzle for tubes

This nozzle features a 1/4 turn gesture for the opening. The cap will stay on the tube while the formula flows through the central orifice. After using the product, the user simply turn the cap to close it.

PRODUCT STORY

1/4 turn nozzle for plastic and Purefoil tubes The nozzle is great for precise application. The convenient cap remains assembled on the tube, decreasing the risks of misplacing it. The tube is hygienic as residual formula is evacuated of the nozzle when it is closed. The ribbed surface of the cap provides the needed grip to close it.

TECHNICAL INFORMATION

Nozzle available with:

- Diameters 30mm to 40mm
- Filling capacity: 30ml to 175ml

CUSTOMER BENEFITS

The 1/4 turn nozzle is easy to open and close with no risk of misplacing it. It has no detachable parts, making life easier for the user. After usage, residual formula is evacuated from the nozzle so the tube is hygienic. Click sound adds excitement and is reassuring to usage.